Twist-Lock® Devices 30A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding



# Watertight Safety-Shroud® Plug

# Features

- Impact resistant shroud protects blades against bending and breaking.
- Reduces exposure to arcing when connecting or disconnecting under load.
- Superior cord grip design protects terminations from excess strain.

#### **Ordering Information**

Description	Cord Diameter	UPC	Catalog Number
Black PBT housing,	.350"-1.150" (9-29)	783585231846	HBL2721SW
white PBT clamps.			

#### Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42 UL Listed, CSA Certified to Type 4, 4X and Type 12

### **Specifications**

Housing / Cord Clamp	PBT	
Terminal Retainer	Clear polycarbonate	
Blades	Brass	
Terminal Screws	#10-32 Brass (Phillips / Slotted / Robertson)	
Terminal Clamp	Cold rolled steel – nickel plated	
Assembly Screws	Stainless Steel	
Watertight Gland	Neoprene	
Closure Plug	Santoprene	

## Performance

#### Electrical

 Current Interrupting
 Certified for current interrupting at full rated current


 Dielectric Voltage
 Withstands 2,000V minimum

 Mechanical
 #16 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

#### Environmental

FlammabilityV0 per UL94 or CSA 22.2 No.0.17Moisture ResistanceType 4, 4X, 12, IP66 suitabilityOperating TemperaturesMaximum Continuous 75°C; Minimum -40°C (w/o impact)



#### Accessories

Watertight Safety Shroud Connector	HBL2723SW	
Watertight Safety Shroud Receptacle	HBL2720SW	

## Resources

Customer Use Drawing	
eCatalog	

