

Twist-Lock® Devices
30A, 3 Phase 250V AC, 3 Pole, 4 Wire
Grounding

Watertight Safety-Shroud® Reverse
Service Flanged Inlet

HUBBELL

Features

- UL type 4X environmental seal while in use and when closed
- High impact, thermoplastic housing for heavy-duty industrial environments
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use

Ordering Information

Description	Device Color	UPC	Catalog Number
Gray PBT housing and flange	Gray		HBL2725SWR

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42
UL Listed, CSA Certified to Type 4, 4X and Type 12

Specifications

Housing	PBT
Blades	Brass
Terminal Retainer	Clear polycarbonate
Terminal Screws	#10-32 Brass (Phillips / Slotted / Robertson)

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability V0 per UL94 or CSA 22.2 No.0.17
Moisture Resistance Type 4, 4X, 12, IP66 suitability
Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)



Accessories

Watertight Safety Shroud Reverse Service Connector	HBL2723SR
Non-Metallic Backbox	BB2030N
2-Gang Weatherproof Box Adapter Plate	HBL2030AP
Mechanical Interlock	HBLMITL

Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

