Twist-Lock® Devices 30A, 3 Phase 600V AC, 3 Pole, 4 Wire Grounding Safety-Shroud® Plug

HUBBELL

Features

- Impact resistant shroud protects blades against bending and breaking.
- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

Ordering Information

Description Cord Diameter UPC Catalog Number Black and white nylon body, white PBT shroud. Cord Diameter UPC Catalog Number HBL2741S



Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Safety-Shroud® White PBT Housing / Cord Clamp Nylon

Terminal Retainer Clear polycarbonate

Blades Brass

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - nickel plated

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG stranded copper wire only.


Terminal Accommodation Terminals identified in accordance with UL 498


Environmental

Flammability HB or better per UL94 or CSA 22.2 No. 0.6

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)





Accessories

Connector HBL2743

Receptacle - Angle Housing HBL2740AR

Receptacle - Surface Mount HBL2740SR

Receptacle - Semi Flush HBL2740SR2

Resources

Customer Use Drawing eCatalog

