Twist-Lock® Devices 30A, 3 Phase 600V AC, 3 Pole, 4 Wire Grounding

Insulgrip® Flanged Inlet

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

Description	Device color	UPC	Catalog Number
Nylon casing, back	White	783585039411	HBL2745
wired.			

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Flange Nylon

Terminal Retainer Clear polycarbonate

Blades **Brass**

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel - nickel plated

Assembly Screws Steel - nickel plated Mounting Screw Nickel plated brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Withstands 2,000V minimum Dielectric Voltage

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

HB or better per UL94/CSA 22.2 No.0.17 Flammability


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C. Minimum -40°C (w/o impact)

HUBBELL







Accessories

Connector	HBL2743
Weatherproof Lift Cover	WP2

Resources

Customer Use Drawing eCatalog

