

Twist-Lock® Devices
30A, 3 Phase 480V AC, 3 Pole, 4 Wire
Grounding
Corrosion Resistant Insulgrip® Connector

Features

- Nickel plated contacts and stainless steel screws provide maximum corrosion resistance.
- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Corrosion resistant, yellow nylon.	.350"-1.150" (9-29)	783585039602	HBL27CM33

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42


Specifications

Housing / Cord Clamp	Nylon
Terminal Retainer	Clear polycarbonate
Contacts	Nickel Plated Brass
Terminal Screws	#10-32 Bronze (Phillips / Slotted / Robertson)
Terminal Clamp	Cold rolled steel – nickel plated
Assembly Screws	Steel - nickel plated

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#16 AWG - #8 AWG stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94 or CSA 22.2 No. 0.6
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C Minimum -40°C (w/o impact)

HUBBELL



Accessories

Plug	HBL27CM31
Weatherproof Boot	HBL60CM36
Flanged Inlet	HBL2735
Weatherproof Boot	HBL60CM35

Resources

Customer Use Drawing
eCatalog

