Twist-Lock® Devices 30A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding

Safety-Shroud® Receptacle

Features

- Accepts Hubbell shrouded and standard NEMA locking plugs
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Engineered thermoplastic housing is impact and corrosion resistant, making it suitable for heavy-duty industrial environments

Ordering Information

Description Device Color UPC Catalog Number RPT angle housing, Gray 783585235042 HBL2810AR one gang.

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Flange Gray RPT
Terminal Retainer Clear polycarbonate
Body Contact Carrier Natural (white) nylon
Body Holding Screws Steel, zinc plated
Contacts Brass
Mounting Plate Steel, zinc plated

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability V2 or better per UL94/CSA 22.2 No.0.17


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

HUBBELL







Accessories

Plug HBL2811S

Resources

Customer Use Drawing eCatalog

