

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Superior cord grip design protects terminations from excess strain

Ordering Information

| Description | Cord Diameter | UPC Number | Catalog Number |
|------------------------|----------------------|-------------|----------------|
| Black and white nylon. | 350"-1.150" (9-29) 7 | 78358568159 | HBL2811ST |

Listings

Listed to UL 498
 Fed.Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------------|-----------------------|
| Housing / Cord Clamp | Nylon |
| Terminal Retainer | Nylon |
| Plunger | Nylon |
| Blades | Copper Alloy |
| Terminal Spring Clamp | Spring Steel |
| Assembly Screws | Zinc Plated Tri-drive |
| Weight (lbs) | 0.35 |

Performance**Electrical**

| | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 3,000V minimum |

Mechanical

| | |
|-------------------------|--|
| Terminal Accommodation | #14 AWG - #8 AWG stranded copper wire only |
| Terminal Identification | Terminals identified in accordance with UL 498 |

Environmental

| | |
|------------------------|---|
| Flammability | HB or better per UL94/CSA 22.2 No.0.17 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C, Minimum -40°C (w/o impact) |

**Online Resources**

Customer Sales Drawings
 eCatalog
 Installation Instructions