## Twist-Lock® Devices 30A, 3 Phase Y 277/480V AC, 4 Pole, 5 Wire Grounding

# HUBBELL

# Watertight Safety-Shroud® Plug

#### **Features**

- UL Type 4X Environmental seal protects connection while in use.
- Impact resistant shroud protects blades against bending and breaking.
- Reduces exposure to arcing when connecting or disconnecting under load.
- Superior cord grip design protects terminations from excess strain.

### **Ordering Information**

Description UPC Catalog Number Cord Diameter Black PBT housing, .350"-1.150" (9-29) 783585454979 HBL2821SW white PBT clamps.



Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

UL Listed, CSA Certified to Type 4, 4X and Type 12

**Specifications** 

Housing / Cord Clamp **PBT** 

Terminal Retainer Clear polycarbonate

Blades **Brass** 

#10-32 Brass (Phillips / Slotted / Robertson) **Terminal Screws** 

**Terminal Clamp** Cold rolled steel - nickel plated

Assembly Screws Stainless Steel Watertight Gland Neoprene Closure Plug Santoprene

**Performance** 

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

**Terminal Accommodation** #16 AWG - #8 AWG stranded copper wire only.

Terminals identified in accordance with UL 498 Terminal Identification

**Environmental** 

Flammability V0 per UL94 or CSA 22.2 No.0.17 Moisture Resistance Type 4, 4X, 12, IP66 suitability

**Operating Temperatures** Maximum Continuous 75°C Minimum -40°C (w/o impact)



Accessories

Watertight Safety Shroud HBL2823SW Connector

Watertight Safety Shroud HBL2820SW

Receptacle

Resources

eCatalog

