

Locking Devices

Watertight Safety Shroud Twist-Lock

30A, 3 Phase Y 277/480V AC; 4 Pole Watertight Safety-Shroud Connector

HUBBELL

Ordering Information

Description	UPC	Catalog Number
Black Valox® housing, white Valox® clamps.	783585456676	HBL2823SW

Specifications

Current/Amperage	30 A
NEMA Rating	NEMA L22-30R

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Flammability	V0 or better per UL94/CSA 22.2 No.0.17
Terminal Accommodation	#16 AWG - #8 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498

Environmental

Moisture Resistance	Type 4, 4X, 12, IP66 suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

