Twist-Lock® Devices 30A, 3 Phase Y 347/600V AC, 4 Pole, 5 Wire Grounding

Watertight Safety-Shroud® Receptacle

Features

- UL type 4X environmental seal while in use and when closed
- High impact, thermoplastic housing for heavy-duty industrial environments
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use

Ordering Information

Description Device Color **UPC** Catalog Number PBT housing and 783585128917 HBL2830SW Gray flange.

Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42

UL Listed, CSA Certified to Type 4, 4X and Type 12

Specifications

Gray RPT Housing / Cover Terminal Retainer Clear polycarbonate **Body Contact Carrier** Natural (white) nylon **Drive Screws** Steel, zinc plated Contacts **Brass**

Lift-Cover Spring & Pin Stainless Steel

Performance

Electrical

Certified for current interrupting at full rated current **Current Interrupting** Dielectric Voltage

Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability V2 or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Maximum Continuous 75°C; Minimum -40°C (w/o impact) **Operating Temperatures**

HUBBELL





Accessories

Watertight Safety Shroud Plug HBL2831SW Non-Metallic Backbox BB2030N 2-Gang Weatherproof Box HBL2030AP Adapter Plate

Mechanical Interlock **HBLMITL**

Resources

Customer Use Drawing eCatalog

