Watertight Devices 30A, 125/250V AC, 3 Pole, 4 Wire

Twist-Lock[®] Plug


Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- · Stainless steel hardware and corrosion-resistant connection points





HUBBELL



Ordering Information

DescriptionCord DiameterUPC NumberCatalog NumberThermoplastic elastomer yellow
plug0.375"-1.000"
(9.5-25.4)783585131702HBL28W74

Listings

IP69K rating Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

Body Thermoplastic Elastomer
Blade Holder White Nylon
Terminal Retainer Clear polycarbonate
Blades Nickel plated brass
Core White Nylon
Bushing & Cone Seal Black Elastomer
Gotcha Ring Nylon

Gotcha Ring Nylo
Strain Relief Nut PBT

Terminal Screws Nickel Plated Brass

Performance

Electrical

Current Interrupting Rated for current interruption per UL498 Dielectric Voltage 2500V AC

Max Working Voltage As marked

Temperature Rise 30°C max per UL498 at rated current

Mechanical

Cord Accomodation 0.375"-1.000" (9.5-25.4)

Environmental

Moisture Resistance UL Listed 4, 4X, 12, 6, 6P

Operating temperatures -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized

Complementary Products

Watertight Connector HBL29W74
Watertight Receptacle with Lift Cover HBL69W74

Online Resources

Customer Use Drawing eCatalog Installation Instructions

