# Single Pole Devices and Temporary Power 300A, 600V AC/250V DC Male Plug



#### Features

- Insulgrip® Style Housing for Superior Gripping
- · Non-Conductive Retaining Screw locks contacts in place
- · Large Raised Alignment Arrow aids in the mating of devices



## **Ordering Information**

**Description** 300A, thermoplastic elastomer, cable size #6 - 2/0 AWG Device Color Black UPC 783585578705


Catalog Number HBL300MBKM1

## Standards

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

## **Specifications**

Base Compound Contact Material Retaining Screw Material Thermoplastic Elastomer Brass Nylon



## Performance

**Electrical** Amperage Rating Voltage Ratings

Mechanical Product Identification 400A Maximum 600V AC Maximum; 250V DC Maximum

Ratings are a permanent part of device #6 to 2/0 AWG

Environmental Flammability HB per UL94 or CSA 22.2. 0.17

**Online Resources** 

**Terminal Accommodation** 

eCatalog

