#### UL 1686 C1 Pin and Sleeve

# 100A, 600/250V AC/DC, 2 Pole, 3 Wire

# Reversed Service Insulgrip® Connector

## **Features**

- O Ring seal provides a watertight and dust tight seal, prevents contamination from entering wire chamber
- Closure cap with neoprene gasket for 4X watertight seal when not in use
- Lid Stay allows for a hands free means of holding the cover in the open position

**Catalog Number** 

HBL3100CS2WR

All-Brass sleeve contacts provide reliable electrical contact

## Ordering Information

**Description**Watertight Insulgrip Connector, 783585012018

Reversed Service

Device Color Grounding Style

Aluminum Style 2

#### **Standards**

UL Standard 1682

CSA Certified to CSA Spec. C22.2 No. 182.1 UL Listed and CSA Certified Type 4X

## **Specifications**

Housing Valox® 357

Connector Shroud Epoxy Painted Aluminum
Cord Clamps Rynite® SST35
Clamp Nut Nickel Plated Brass

Gland Neoprene

#### **Performance**

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC Max. Working Voltage 600V AC RMS

Mechanical

Impact Resistance Per CSA C22.2, No. 182.1, UL 1682

Product Identification Identification and ratings are permanently fastened

to the device housing

Terminal Identification Terminals identified in accordance with UL 1686(1,

2, 3, Green)

**Environmental** 

Flammability (Enclosure) UL 94V-0 and CSA C22.2 No. 0.17

Moisture Resistance Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94
Operating Temperatures Max. Continuous 75°C; Min. -40°C w/o impact -25°

with impact

### **Accessories**

Cord Clamps and Locking Ring

## Online Resources

Customer Use Drawing eCatalog

Installation Instructions







