## UL 1686 C1 Pin and Sleeve

## 30A, 600/250V AC/DC, 2 Pole, 3 Wire

# **Reversed Service Insulgrip® Connector**

## Features

- O Ring seal provides a watertight and dust tight seal, prevents contamination from entering wire chamber
- Closure cap with neoprene gasket for 4X watertight seal when not in use
- Lid Stay allows for a hands free means of holding the cover in the open position
- · All-Brass sleeve contacts provide reliable electrical contact

## **Ordering Information**

Description Watertight Insulgrip Connector, Reversed Service	<b>UPC</b> 783585012094	Catalog Number HBL330CS1WR
Device Color Aluminum	Grounding Style Style 1	

#### Standards

UL Standard 1682 CSA Certified to CSA Spec. C22.2 No. 182.1 UL Listed and CSA Certified Type 4X

### Specifications

Housing Connector Shroud Cord Clamps Clamp Nut Gland Valox® 357 Epoxy Painted Aluminum Rynite® SST35 Nickel Plated Brass Neoprene

## Performance

Electrical Current Interrupting

Dielectric Voltage

Max. Working Voltage

#### Mechanical

Impact Resistance Product Identification

Terminal Identification

#### Environmental

Flammability (Enclosure) Moisture Resistance Operating Temperatures Certified for current interrupting at full rated current

Withstands 3,000V AC 600V AC RMS

Per CSA C22.2, No. 182.1, UL 1682 Identification and ratings are permanently fastened to the device housing Terminals identified in accordance with UL 1686(1, 2, 3, Green)

UL 94V-0 and CSA C22.2 No. 0.17 Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94 Max. Continuous 75°C; Min. -40°C w/o impact -25° with impact

#### Accessories

Cord Clamps and Locking Ring

## **Online Resources**

Customer Use Drawing eCatalog Installation Instructions

Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.







