# IEC Pin and Sleeve 30A, 240V, 2 Pole, 3 Wire

## **Mechanical Interlock**

# HUBBELL

#### **Features**

- Plug cannot be removed until the switch is turned off.
- Large gears enclosed in a gear box
- · Lockable handle to meet OSHA Lockout/Tagout regulations.
- Pre-wired IEC Pin and Sleeve receptacle
- Enclosure Type 4X, 12 and IP67 Suitability

#### **Ordering Information**

**Description**Circuit-Lock® Pin and Sleeve
Mechanical Interlock

**UPC** 783585405827

Catalog Number HBL330MI6W

Color code Blue

#### **Standards**

UL Listed CSA Certified

#### **Specifications**

Face Valox®
Base Valox®
Enclosure Gasket Neoprene
Shaft Seal Neoprene
Conduit Hub Zinc

### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

and voltage

Dielectric Voltage Withstands 3,000V AC Min

Max. Working Voltage 600V AC RMS

Mechanical

Impact Resistance In accordance with UL 746C Mounting External adjustable feet

Product Identification Identification and ratings are part of the external label and molded into the receptacle mount

Terminal Identification In accordance with UL, CSA and international

conventions

**Environmental** 

Flammability UL94-5VA and V-0 Classification

Ingress Protection IP67 Suitability

Moisture Resistance Outdoor - 4X (Watertight, Washdown); Indoor - 12

(Dust-tight, Falling Dirt and Noncorrosive Liquids). Max. Continuous +75°C; Min. Continuous -40°C

#### **Online Resources**

Operating Temperature

Customer Use Drawing

eCatalog

Installation Instructions







