# UL 1686 C1 Pin and Sleeve

### 30A, 600/250V AC/DC, 2 Pole, 3 Wire

## Insulgrip® Pin and Sleeve Plug

#### **Features**

- Impact resistant shroud protects sleeves from bending and
- Locking ring provides UL Type 4X watertight, dust-tight seal
- Catalog number and rating visible while in use
- All-Brass sleeve contacts provide reliable electrical contact

#### **Ordering Information**

Description Pin and Sleeve, Watertight Insulgrip Plug

783585010007

Catalog Number HBL330PS1W

**Device Color** 

**Grounding Style** 

Aluminum

Style 1



UL Standard 1682, UL 50, and UL 1010 CSA Certified to CSA Spec. C22.2 No. 159 UL Listed and CSA Certified Type 4X

#### **Specifications**

Housing Valox® 357 Plug Shroud Aluminum

Clamp Nut Nickel Plated Brass Gland Cap Rynite® SST35 Thermoset Polyester Retainer

O-Ring, Gaskets & Seals Neoprene

#### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Withstands 3,000V AC Dielectric Voltage Max. Working Voltage 600V AC RMS

Mechanical

Per CSA C22.2, No. 182.1, UL 1682 Impact Resistance

**Product Identification** Identification and ratings are permanently fastened

to the device housing

**Terminal Identification** Terminals identified in accordance with UL 1686(1,

2, 3, Green)

**Environmental** 

UL 94V-0 and CSA C22.2 No. 0.17 Flammability (Enclosure)

Moisture Resistance Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94 **Operating Temperatures** Max. Continuous 75°C; Min. -40°C w/o impact -25°

with impact

#### **Accessories**

Cord Clamps and Locking Ring

Liquidtight Adapters

#### Online Resources


Customer Use Drawing

eCatalog

Installation Instructions



HUBBELL





Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

