UL 1686 C1 Pin and Sleeve

60A, 600/250V AC/DC, 2 Pole, 3 Wire

Reversed Service Insulgrip® Connector

Features

- O Ring seal provides a watertight and dust tight seal, prevents contamination from entering wire chamber
- Closure cap with neoprene gasket for 4X watertight seal when not
- Lid Stay allows for a hands free means of holding the cover in the open position
- All-Brass sleeve contacts provide reliable electrical contact

Ordering Information

UPC Description **Catalog Number** Watertight Insulgrip Connector, 783585012179 HBL360CS2WR

Reversed Service

Device Color Grounding Style

Aluminum Style 2

Standards

UL Standard 1682

CSA Certified to CSA Spec. C22.2 No. 182.1 UL Listed and CSA Certified Type 4X

Specifications

Valox® 357 Housing

Connector Shroud **Epoxy Painted Aluminum Cord Clamps** Rynite® SST35 Clamp Nut Nickel Plated Brass

Gland Neoprene

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC 600V AC RMS

Max. Working Voltage

Mechanical

Impact Resistance Per CSA C22.2, No. 182.1, UL 1682

Product Identification Identification and ratings are permanently fastened

to the device housing

Terminal Identification Terminals identified in accordance with UL 1686(1,

2, 3, Green)

Environmental

Flammability (Enclosure) UL 94V-0 and CSA C22.2 No. 0.17

Moisture Resistance Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94 **Operating Temperatures** Max. Continuous 75°C; Min. -40°C w/o impact -25°

with impact

Accessories

Cord Clamps and Locking Ring

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

HUBBELL





