Twist-Lock® Devices 50A, 250V DC, 600V AC, 2 Pole, 3 Wire Grounding Flanged Inlet

HUBBELL

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Ordering Information

Description Device Style UPC Catalog Number
Zinc plated steel Metallic 783585236445 HBL3767
casing, thermoset interior with lift cover



Listings

Listed to UL 498 Certified to CSA C22.2 No.42

Specifications

Casing	Steel, zinc plated
Terminal Retainer	Phenolic
Blades	Brass
Terminal Screws	Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage Withstands 2,000V minimum

Pielectific voltage vvittistands 2,000 v minimul


Mechanical

Terminal Accommodation #10 AWG - #6 AWG solid or stranded copper wire only

Environmental

Flammability UL 94 V0

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Connector	HBL3762C
-----------	----------

Resources

Customer Use Drawing eCatalog

