# Single Pole Devices and Temporary Power 400A, 600V AC/DC Female Plug



#### Features

- Extra Long non-conductive inner sleeve
- · Turn and Lock Symbol aids in the mating of devices
- · Easily Identifiable Cable with cut off points for secure fit

### **Ordering Information**

**Description** 400A, thermoplastic elastomer, cable size 2/0 -4/0 AWG

**Device Color** Orange

UPC Number Catalog Number 783585399645 HBL400FO



#### Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

#### **Specifications**

Base Compound Contact Material Retaining Screw Material Thermoplastic Elastomer Brass Nylon

## Performance

**Electrical** Amperage Rating Voltage Rating


400A Maximum 600V AC/DC Maximum

Mechanical Product Identification Terminal Accommodation

Ratings are a permanent part of device 2/0 to 4/0 AWG

Environmental Flammability

HB per UL94 or CSA 22.2. 0.17



#### Online Resources

Customer Sales Drawings eCatalog Installation Instructions



**Wiring Device-Kellems**