Single Pole Devices and Temporary Power 400A, 600V AC/DC

Female Plug

HUBBELL

Features

- Extra Long non-conductive inner sleeve
- Turn and Lock Symbol aids in the mating of devices
- · Easily Identifiable Cable with cut off points for secure fit

Ordering Information

Description 400A, thermoplastic elastomer, cable size 2/0 -4/0 AWG

Device Color Yellow

UPC Number 783585112251

Catalog Number HBL400FY



Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

Specifications

Base Compound Thermoplastic Elastomer

Contact Material Brass Retaining Screw Material Nylon

Performance

Electrical

Amperage Rating 400A Maximum Voltage Rating 600V AC/DC Maximum


Mechanical

Product Identification Ratings are a permanent part of device

Terminal Accommodation 2/0 to 4/0 AWG

Environmental

HB per UL94 or CSA 22.2. 0.17 Flammability



Online Resources

Customer Sales Drawings eCatalog Installation Instructions

