# Single Pole Devices and Temporary Power 400A, 600V AC/DC

### Male Plug

## HUBBELL

#### **Features**

- Insulgrip® Style Housing for Superior Gripping
- Non-Conductive Retaining Screw locks contacts in place
- · Large Raised Alignment Arrow aids in the mating of devices

#### **Ordering Information**

**Description** 400A, thermoplastic elastomer, cable size 2/0 -4/0 AWG **Device Color** Brown **UPC Number** 783585112282

Catalog Number HBL400MBN

#### Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

#### **Specifications**

Base Compound

Thermoplastic Elastomer

Contact Material
Retaining Screw Material

Brass Nylon

#### **Performance**

**Electrical** 

Amperage Rating Voltage Rating

400A Maximum 600V AC/DC Maximum

Mechanical

Product Identification Terminal Accommodation


Ratings are a permanent part of device

2/0 to 4/0 AWG

**Environmental** 

Flammability HB per UL94 or CSA 22.2. 0.17





#### **Online Resources**

Customer Sales Drawings eCatalog Installation Instructions

