IEC Pin and Sleeve

100/125A, 380-415V, 3 Pole, 4 Wire

Watertight Plug

Features

- UL Type 4X, 12 and IP69k environmental ratings
- One piece non-metallic housing provides impact and chemical resistance in an insulated body
- Watertight neoprene gland seal to prevent water ingress from entering at cable entrance
- Solid one-piece pins for reliable electrical contact
- Sequential contact engagement to prevent a momentary over-voltage

Ordering Information

Description **UPC** Catalog Number Watertight IEC Pin and Sleeve 783585574943 HBL4100P6W Mating Plug

Listings

UL Listed, File E146033 CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2

Specifications

PBT Housing **PBT** Locking Ring Solid Neoprene Sealing Gasket

Contact Carrier **High-Impact Thermoset**

Glands Santoprene Stainless Steel **Terminal Screws**

Cord Clamps **PBT**

Performance

Electrical

Certified for current interrupting at full rated **Current Interrupting**

current

Dielectric Voltage Withstands 3,000V AC 600V AC RMS Max. Working Voltage

Mechanical

Impact Resistance Per CSA C22.2 No.182.1 /UL1682

Identification and ratings are a permanent part of **Product Identification**

the device housing.

Terminal Identification Terminals identified in accordance with North

American and IEC conventions

Environmental

Flammability

Ingress Protection Type 3R,3RX,4X and IP68,IP69K Moisture Resistance

IEC 60309-1

Operating Temperature Maximum Continuous 75°C; Minimum - 40°C

w/o impact

Complementary Products

Closure Cap

Cord Clamp and Locking Ring

Liquidtight Adapters

Online Resources

Customer Sales Drawing

eCatalog

Installation Instructions

HUBBELL





