## **IEC Pin and Sleeve**

30A, 3 Phase, 240V, 3 Pole, 4 Wire

# **Reverse Service Mechanical Interlock**

#### Features

- · Reverse service plug cannot be removed under load.
- · Captured neoprene gasket for a watertight seal
- · Lockable handle to meet OSHA Lockout/Tagout regulations.
- · Solid pins for longer life and reliable electrical contact
- Enclosure Type 4X, 12 and IP67 Suitability

### Ordering Information

 Description
 UPC

 Circuit-Lock® Reverse Service
 783585012605

 Mechanical Interlock
 783585012605

Catalog Number HBL430MI9WR

Color code Blue

#### Standards

UL Listed CSA Certified

#### Specifications

Face Base Enclosure Gasket Shaft Seal Conduit Hub Valox® Valox® Neoprene Neoprene Zinc

Withstands 3,000V AC Min

In accordance with UL 746C

UL94-5VA and V-0 Classification

External adjustable feet

and voltage

600V AC RMS

conventions

IP67 Suitability

Certified for current interrupting at full rated current

Identification and ratings are part of the external label and molded into the receptacle mount

Outdoor - 4X (Watertight, Washdown); Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liguids).

Max. Continuous +75°C; Min. Continuous -40°C

In accordance with UL, CSA and international

## Performance

Electrical Current Interrupting

Dielectric Voltage Max. Working Voltage

#### Mechanical

Impact Resistance Mounting Product Identification

Terminal Identification

#### Environmental

Flammability Ingress Protection Moisture Resistance

**Operating Temperature** 

**Online Resources** 

Customer Use Drawing eCatalog Installation Instructions







