## **IEC Pin and Sleeve**

30A, 3 Phase, 240V, 3 Pole, 4 Wire

# **Reverse Service Plug**

### Features

- UL Type 4X, 12 and IP69k environmental ratings
- One piece non-metallic housing provides impact and chemical resistance in an insulated body
- Watertight neoprene glad seal to prevent water ingress from entering at cable entrance
- Sequential contact engagement to prevent a momentary over-voltage
- Heavy duty external cord grips for maximum cord retention

current

600V RMS

Withstand 3000V AC

the device housing

### **Ordering Information**

DescriptionUPCWatertight IEC Pin and Sleeve783585012711Mating Plug- Reversed Service783585012711

### Listings

UL Listed, File E146033 CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2

### **Specifications**

Housing Locking Ring Sealing Gasket Contact Carrier Glands PBT PBT Solid Neoprene High-Impact Thermoset Santoprene

Certified for current interrupting at full rated

Per CSA C22.2 No. 182.1 / UL1682

American and IEC conventions

### Performance

#### Electrical

Current Interrupting

Dielectric Voltage Max. Working Voltage

### Mechanical

Impact Resistance Product Identification

Terminal Identification

#### Environmental

Flammability Ingress Protection Moisture Resistance Operating Temperatures V-0 Type 3R, 3RX, 4X and IP68, IP69K IEC 60309-1 Maximum Continuous 75°C; Minimum - 40°C w/o impact

Identification and ratings are a permanent part of

Terminals identified in accordance with North

### **Complementary Products**

Cover Assemblies Cord Clamp and Locking Ring Liquidtight Adapters


### **Online Resources**


Customer Sales Drawing eCatalog Installation Instructions

Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.











rmoset

Catalog Number HBL430P9WR