# Twist-Lock® Devices 15A, 250V, 2 Pole, 3 Wire Grounding Insulgrip® Flanged Inlet

# HUBBELL

#### **Features**

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

### **Ordering Information**

Description Device Color UPC Catalog Number Nylon casing, back White 783585170206 HBL4586C wired.

## Listings

Listed to UL 498 Fed.Spec.W-C-596 Certified to CSA C22.2 No.42

# **Specifications**

Housing Nylon

Terminal Retainer Clear polycarbonate

Blades Brass

Terminal Clamp #8-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - zinc plated Mounting Screw Nickel plated brass

#### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #10 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498


**Environmental** 

Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)





#### **Accessories**

Connector HBL4579C
Weatherproof Lift Cover WP1

#### Resources

Customer Use Drawing eCatalog

