IEC Pin and Sleeve

60A, 3 Phase, 480V, 3 Pole, 4 Wire

Reverse Service Plug

Features

- UL Type 4X, 12 and IP69k environmental ratings
- One piece non-metallic housing provides impact and chemical resistance in an insulated body
- Watertight neoprene gland seal to prevent water ingress from entering at cable entrance
- Heavy duty external cord grips for maximum cord retention
- Sequential contact engagement to prevent a momentary overvoltage

Ordering Information

Description	UPC	Catalog Number
Watertight IEC Pin and Sleeve	783585012742	HBL460P7WR
Mating Plug- Reversed Service		

Standards

UL Listed, File E146032 CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2

Specifications

Housing Locking Ring Sealing Gasket Contact Carrier **Terminal Screws** Retainer

PBT PBT Solid Neoprene High-Impact Thermoset Stainless Steel High-Impact Thermoset

Certified for current interrupting at full rated current

Identification and ratings are a permanent part of the

Terminals identified in accordance with North

HB or Better per UL 94 or CSA C22.2 No. 0.17

Maximum Continuous 75°C; Minimum - 40°C w/o

Withstands 3,000V AC Min

Per CSA C22.2 No. 182.1 / UL1682

American and IEC conventions

Watertight per IEC 60309-1

600V AC RMS

device housing.

IP67 Suitability

impact

Performance

Electrical Current Interrupting

Dielectric Voltage Max. Working Voltage

Mechanical

Impact Resistance Product Identification


Terminal Identification

Environmental

Flammability Ingress Protection Moisture Resistance **Operating Temperature**

Online Resources

Customer Use Drawing eCatalog Installation Instructions





Wiring Device-Kellems



