Twist-Lock® Devices 15A, 125V, 2 Pole, 3 Wire Grounding Valise® Connector

HUBBELL

Features

- Two captive multiple drive assembly screws
- Totally insulated impact and crush resistant nylon body
- Powerful cord grips prevent conductor slippage and strain on wiring terminals





Ordering Information

Description Cord Diameter UPC Catalog Number 783585043289 HBL4729VBK (5.6-16.8)

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing Nylon

Cable Inserts Polyphenylene Oxide

Contacts Brass

Terminal Screws #6-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - Zinc plated

2 19/32 1 1 1 DIA.

Performance

Electrical

Current Interrupting Certified for full rated current Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #12 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL 94 or CSA 22.2 No. 0.6

Moisture Resistance IP20 Suitability

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o impact)

Accessories

Plug	HBL4723VBK
Flanged Inlet	HBL4716C

Resources

Customer Use Drawing eCatalog

