

Twist-Lock® Devices
15A, 277V AC, 2 Pole, 3 Wire Grounding
Stainless Steel Flanged Inlet

HUBBELL

Features

- Heat resistant thermoset construction
- Stainless steel casing
- #5-40 terminal screws
- Mounting screws included

Ordering Information

Description	Device Color	UPC	Catalog Number
Stainless steel casing, brown phenolic	Brown/Stainless	783585236988	HBL4786

Listings


Listed to UL 498
Fed.Spec.W-C-596
Certified to CSA C22.2 No.42

Specifications

Flange	Stainless steel
Blades	Brass
Terminal Screws	Brass
Mounting Screw	Nickel plated brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#18 AWG - #10 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Connector	HBL4779C
-----------	----------

Resources

Customer Use Drawing
eCatalog

