

Power Quality & Conversion
Service/Branch Panels
Wired-In Surge Arrestors, Single Phase and Three Phase (Type 1 SPD)

HUBBELL

Features

- 40KA
- 120/208 VAC
- 3 Phase Y, Type 1

Ordering Information

Description	UPC	Catalog Number
Wired-In Surge Arrestors, Single Phase and Three Phase (Type 1 SPD)	783585833118	HBL4SA40



Listings

cULus Listed

Specifications

Max. Surge Current per Phase:	40kA
Max. Operating Temperature:	-40°F to 149°F (-40°C to 65°C)
Diagnostics Indicators:	Green Status LED per line
Dimensions:	3.60"W x 3.0"H x 2.64"D
Weight:	1.8 lbs.
Terminal Accommodation:	#12 AWG Wire Leads
Frequency:	50/60 Hz
EMI/RFI:	Up to -30dB
Housing Rating:	Type 4X
Listing:	UL1449 4th edition
Warranty:	2 year

