## Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Flanged Inlets

# HUBBELL

#### **Features**

- Stainless steel flange
- Minature style
- Mounting screws included

#### **Ordering Information**

Description Device Color Catalog Number Stainless steel flange, Brown 783585013138 HBL5240 phenolic body, miniature style

#### Listings

UL Listed, File E2186 Certified to CSA, C22.2, No. 42 **NEMA® WD-6 Compliant** 

#### **Specifications**

Face Phenolic Blades .040" (1.0) Brass **Terminal Screw** #5-40 Brass, straight Mounting Screw Nickel plated brass

### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Withstands 2,000V minimum Dielectric Voltage

Mechanical

Product Identification Ratings are a permanent part of the device **Terminal Accommodation** #18-#14 AWG copper stranded or solid wire only


**Terminal Identification** Terminals identified in accordance with UL 498 and CSA

**Environmental** 

Flammability UL 94 V-0

**Operating Temperatures** Maximum continuous 75°C; minimum -40°C (w/o impact)





### Resources

Customer Use Drawing eCatalog

