

## Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

# Heavy Duty, Specification Grade Tamper-Resistant Duplex Receptacles

# HUBBELL

## Features

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Brass mounting strap and Triple Wipe contacts
- High impact resistant face with circuit I.D. marking area
- Complies with National Electrical Code (NEC®) requirements for Tamper Resistant receptacles

## Ordering Information

Description	Device Color	UPC Number	Catalog Number
Fed-Spec listed, Smooth nylon face, back and side wired, duplex	Brown	783585542416	HBL5262TR

## Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

## Specifications

Face	Nylon
Base	PBT
Power Contacts	Brass
Ground Contact	Brass
Clamping Plate	Plated steel
Mounting Strap	Brass
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

## Performance

### Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#12-10 AWG stranded or solid copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

### Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



## Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

