

IEC Pin and Sleeve

30A, 3 Phase Y, 347/600V, 4 Pole, 5 Wire

Watertight Receptacle

- Features
- UL Type 4X, 12 and IP69k environmental ratings
  - Super tough insulated non-metallic housing
  - Self-closing gasketed cover
  - Sequential contact engagement to prevent a momentary over-voltage
  - Market leading UL witnessed HP ratings

Ordering Information

Description	UPC	Catalog Number
Watertight IEC Pin and Sleeve Receptacle	783585405506	HBL530R5W

Listings

UL Listed, File E146032  
CSA Certified File LR285C  
UL Classified to IEC 60309-1 IEC 60309-2219

Specifications

Housing	PBT
Closure Covers	PBT
Sealing Gasket	Solid Neoprene
Retainer	High-Impact Thermoset
Gaskets	Santoprene
Terminal Screws	Stainless Steel

Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V RMS
<b>Mechanical</b>	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
<b>Environmental</b>	
Flammability	V-0
Ingress Protection	TYPE 3R,3RX,4X AND IP68,IP69K
Moisture Resistance	IEC 60309-1
Operating Temperatures	Maximum Continuous 75°C; Minimum - 40°C w/o impact

Complementary Products

Cover Assemblies

Online Resources

Customer Sales Drawing  
eCatalog  
Installation Instructions

HUBBELL

