

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

## Load:Logic® Load Control Receptacles

### Features

- Designed for Automatic Receptacle (plug load) Control
- Duplex controlled face and downstream control
- Low voltage wire control
- Tamper Resistant... NOT Plug Resistant®

### Ordering Information

| Description                | Device Color | UPC Number   | Catalog Number |
|----------------------------|--------------|--------------|----------------|
| Decorator face, back wired | Gray         | 783585427799 | HBL5362LC2GY   |

### Listings

cULus 498B SA UL File No. E481574  
Fed. Spec. WC596G  
Complies with:NEC Section 406.3 (E), ASHRAE 90.1 Section 8.4.2,California Title 24  
Artcile 130.5(d)  
NEMA WD-6 Compliant

### Specifications

|                        |                                   |
|------------------------|-----------------------------------|
| Face                   | Nylon                             |
| Base                   | Nylon                             |
| Power Contacts         | 0.031in (0.8) Brass               |
| Wire Clamp             | 0.062in (1.6) Steel-Nickel Finish |
| Mounting Strap         | 0.047in (1.2) Brass               |
| Terminal Screws        | #8-32 Brass, Multiple Drive       |
| Self -Grounding Staple | Stainless Steel                   |
| Mounting Screws        | Zinc-Plated Steel                 |

### Performance


**Electrical**  
Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

**Mechanical**  
Product Identification Ratings are a permanent part of the device  
Terminal Accomodation #14-10 AWG stranded or solid copper conductor only  
Terminal Identification Terminals identified in accordance with UL498 and CSA (Brass, White, Green)

**Environmental**  
Flammabilty UL94V-2  
Operating Location Indoor Use Only  
Operating Temperature 0° to 40°C (32° to 104°F) Relative Humidity (non-condensing) 0% to 95% (w/o impact)

# HUBBELL



### Complementary Products

|   |        |
|---|--------|
| Wallplate, Decorator Opening, Nylon           | NP26GY |
| Wallplate, Decorator Opening, Stainless Steel | SS26   |

### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

