Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Insulgrip Plug

HUBBELL

Features

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

Ordering Information

Description	Cord Diameter .230"720"(5.8-18.	UPC	Catalog Number
Black nylon		783585036533	HBL5366CM2
	3)		

Listings

UL Listed to UL498 File E1706 CSA Certified to C22.2 No. 42 File 280 Fed. Spec. W-C596G NEMA® WD-6 Compliant

Specifications

Housing/Cord Clamp Nylon
Blade Holder Nylon

Terminal Retainer Clear Polycarbonate
Blades .060 in. (1.5) Brass
Terminal Screws #8-32 Brass , multiple drive

Terminal Clamp

Assembly Screws

Nickel plated steel

Nickel plated steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Cord Accomodation .230"-.720"(5.8-18.3)

Terminal Accommodation #18-10 AWG. Standed copper wire only

Terminal Identification Terminals identified in accordance with UL 498 and CSA


Environmental


Flammability UL 94 HB or better

IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)







Accessories

Weatherproof Boot HBL6017

Resources

Customer Use Drawing eCatalog

