

Straight Blade Devices  
15A, 125V, 2 Pole, 2 Wire Non-Grounding  
Valise® Plug

HUBBELL

Features

- Replacement plug for vacuum cleaners
- Hinged one piece body design for easy assembly
- Powerful cord grips prevent conductor slippage and strain
- Polarized blades

Ordering Information

Description	Device Color	UPC	Catalog Number
Black nylon, polarized	Black	783585366074	HBL5867VBLK

Listings

UL Listed to UL498 File E1706  
CSA Certified to C22.2 No. 42 File 280C  
NEMA® WD-6 Compliant

Specifications

Housing	Nylon
Blades	Brass
Assembly Screws	Plated Steel
Cable Inserts	PPO
Terminal Screws	Brass
Terminal Clamp	Nickel plated steel
Assembly Screws	Plated steel

Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
<b>Mechanical</b>	
Product Identification	Molded Rating on Device Face
Terminal Accommodation	#18-#14 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
<b>Environmental</b>	
Flammability	UL 94 HB
IP Suitability	IP20
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Customer Use Drawing  
eCatalog

