Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Valise Plug



Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

Ordering Information

Description Gray nylon	Cord Diameter .220"660"(5.6-16. 8)	UPC 783585013268	Catalog Number HBL5965VGY
	0)		

Listings

UL Listed to UL498 File E1706 CSA Certified to C22.2 No 42 File 280C NEMA® WD-6 Compliant

Specifications

Housing	Nylon
Blades	Brass
Assembly Screws	Plated Steel
Cable Inserts	PPO
Terminal Screws	#8-32 Brass, multiple drive
Terminal Clamp	Nickel plated steel
Assembly Screws	Plated steel



Electrical

Mechanical

Environmental

Flammability


IP Suitability

Current Interrupting Dielectric Voltage Certified for current interrupting at full rated current Withstands 2,000V minimum

Product IdentificationRatings are a permanent part of the deviceTerminal Accommodation#18-#12 AWG stranded copper wire onlyTerminal IdentificationTerminals identified in accordance with UL 498 and CSA

UL 94 HB or better IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Customer Use Drawing eCatalog



Wiring Device-Kellems