Watertight Devices 15A, 125V, 2 Pole, 3 Wire **Duplex Receptacle**



Features

- Impact resistant PBT lid, cover plate, and receptacle body
- Thermoplastic elastomer seal ٠
- Stainless steel hardware and corrosion-resistant connection points

Ordering Information

Description Thermoplastic elastomer yellow Yellow receptacle

Device Color UPC Number

Catalog Number 783585528700 HBL60W47D

ŪĠ

Listings

IP69K rating Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

Body **Contact Carrier Terminal Retainer** Contacts Core **Terminal Screws** Hardware

PBT White Nylon Clear polycarbonate Nickel plated brass White Nylon Nickel plated brass Stainless Steel

Performance

Electrical

Current Interrupting Dielectric Voltage Max Working Voltage **Temperature Rise**

Environmental

Moisture Resistance Operating temperatures UV resistance

Rated for current interruption per UL498 2500V AC As marked 30°C max per UL498 at rated current

UL Listed 4, 4X, 12, 6, 6P -40°C (without impact) to +60°C continuous All exposed materials are UV stabilized

Online Resources


Watertight Plug

Complementary Products

Customer Use Drawing eCatalog Installation Instructions







HBL14W47A

Wiring Device-Kellems