# Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Flanged Inlets

# HUBBELL

#### **Features**

- Weatherproof flip lid
- Weatherproof boot covers terminals
- Multiple drive screws
- Nickel plated brass blades

**Ordering Information** 

Description Device Color UPC Catalog Number Weatherproof lift cover 783585808666 HBL61CM64BK Black and boot



UL Listed, File E2186 Certified to CSA, C22.2, No. 42 **NEMA® WD-6 Compliant** 

**Specifications** 

Base Nylon

**Power Contacts** .040" (1.0) Brass

#8-32 Brass, Multiple Drive **Terminal Screws** 

Mounting Screw Stainless steel

### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2.000V minimum

Mechanical

**Product Identification** Ratings are a permanent part of the device


#14-#10 AWG copper stranded or solid conductor only **Terminal Accommodation** Terminal Identification Terminals identified in accordance with UL 498 and CSA


**Environmental** 

Flammability UL 94 V-2

**Operating Temperatures** Maximum continuous 75°C; minimum -40°C (w/o impact)







## Resources

Customer Use Drawing eCatalog

