Watertight Devices

20A, 3 Phase 480V AC, 3 Pole, 4 Wire

Twist-Lock® Receptacle

HUBBELL

Features

- Impact resistant PBT lid, cover plate, and receptacle body
- Thermoplastic elastomer seal
- · Stainless steel hardware and corrosion-resistant connection points

Ordering Information

Description **Device Color** Thermoplastic elastomer black Black receptacle

UPC Number Catalog Number 783585511276 HBL67W76BK

Listings

IP69K rating Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

PBT Body **Contact Carrier** White Nylon Terminal Retainer Clear polycarbonate Contacts Nickel plated brass White Nylon Core **Terminal Screws** Nickel plated brass Stainless Steel Hardware

Performance

Electrical

Current Interrupting Rated for current interruption per UL498 Dielectric Voltage 3500V AC Max Working Voltage As marked


30°C max per UL498 at rated current Temperature Rise


Environmental

UL Listed 4, 4X, 12, 6, 6P Moisture Resistance

Operating temperatures -40°C (without impact) to +60°C continuous **UV** resistance All exposed materials are UV stabilized







Complementary Products

Watertight Plug HBL26W76BK

Online Resources

eCatalog

