Watertight Devices 20A, 120/208V AC, 4 Pole, 5 Wire Twist-Lock [®] Receptacle



Features

- · Impact resistant PBT lid, cover plate, and receptacle body
- · Thermoplastic elastomer seal
- · Stainless steel hardware and corrosion-resistant connection points

Ordering Information

 Description
 Device Color
 UPC Number
 Catalog Number

 Thermoplastic elastomer yellow
 Yellow
 783585433202
 HBL67W81

Listings

IP69K rating Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

Body Contact Carrier Terminal Retainer Contacts Core Terminal Screws Hardware PBT White Nylon Clear polycarbonate Nickel plated brass White Nylon Nickel plated brass Stainless Steel

Performance

Electrical

Current Interrupting Dielectric Voltage Max Working Voltage Temperature Rise

Environmental


Moisture Resistance Operating temperatures UV resistance Rated for current interruption per UL498 2500V AC As marked 30°C max per UL498 at rated current

UL Listed 4, 4X, 12, 6, 6P -40°C (without impact) to +60°C continuous All exposed materials are UV stabilized



Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.





Complementary Products

Watertight Plug

HBL26W81

Online Resources

Customer Use Drawing eCatalog Installation Instructions



Wiring Device-Kellems