

Hospital Products

Power Strips

Heavy Duty Relocatable Power Taps



Features

- Heavy-duty 18 gauge galvanized steel housing with durable powder coat finish
- All models come with built in circuit breaker for over current protection
- Tamper-Resistant Receptacles



Ordering Information

Description	Color	Catalog No.	UPC
Relocatable Power Taps, 15A 125V, 6 Outlet, 6' Cord	Black	HBL6RPT6BK	783585452517

Listings

cULus Listed UL1363 RPT

Specifications

Electrical	
Current	15A
Voltage	125V
Frequency	60Hz
Over Current Protection	15A CB
Physical	
Length	11.12" (282.4)
Width	2.22" (56.4)
Height	1.6" (40.5)
Environmental	
Operating Temperature	-40°F to 160°F (-40°C to 70°C)

