Midget Twist-Lock® Devices 15A, 125/250V AC, 3 Pole, 3 Wire Non-Grounding

Plug

Features

- Abuse resistant nylon housing
- Phenolic body for high heat resistance
- Angled body design for low profile in tight spaces
- Totally insulated body adds extra measure of safety

Ordering Information

| • | | | | |
|-----------------------------------|--|---------------------|---------------------------|--|
| Description Black angled plug. | Cord Diameter .335"421" (8.5-10.7) | UPC 783585237190 | Catalog Number HBL7432 | |
| | | | | |

Listings

Listed to UL 498 Certified to CSA C22.2 No.42

Specifications

| Nylon | |
|-------------|----------------------------------|
| Brass | |
| Phenolic | |
| #5-40 Brass | |
| Nylon | |
| | Brass Phenolic #5-40 Brass |

Withstands 2,000V minimum

Performance

Electrical

Current Interrupting Dielectric Voltage

Mechanical

Terminal Accomodation Terminal Identification

 Environmental
 HB or better per UL94/CSA 22.2 No.0.17

 Flammability
 HB or better per UL94/CSA 22.2 No.0.17

 Moisture Resistance
 IP20 Suitability

 Operating Temperatures
 Maximum Continuous 75°C Minimum -40°C (w/o impact)


Certified for current interrupting at full rated current

#18 AWG - #14 AWG stranded copper wire only.

Terminals identified in accordance with UL 498







Accessories

| Angled Connector | HBL7433 | |
|--|----------|--|
| Nylon Flanged Receptacle | HBL7478N | |
| Stainless Steel Flanged Receptacle | HBL7487 | |
| StainlessSteel Flanged Receptacle with Covered Terminals | HBL7489 | |
| | | |

Resources

| Customer Use Drawing | |
|----------------------|--|
| eCatalog | |

