Straight Blade Devices 50A, 125/250V, 3 Pole, 3 Wire Non-Grounding Connector Body



Features

- Catalog number, ratings and certifications molded in face
- Gripping ribs provide secure gripping area
- Supertough nylon housing



Ordering Information

Description Connector body, Insulgrip, nylon. Cord Diameter UPC .625"-1.218" 7835 (15.9-30.9)


UPC Catalog Number 783585015118 HBL7515C

Listings

UL Listed File E1706 CSA Certified

Specifications

Housing	Supertough Nylon
Blade Holder	Reinforced Thermoplastic Polyester
Blades	Brass
Box Terminals	Copper Alloy
Cord Clamps	Reinforced Thermoplastic Polyester



Performance

Current Interrupting

Dielectric Voltage

Electrical

Certified for current interrupting at full rated current Withstands 2,000V minimum

Mechanical

Product IdentificationRatings are a permanent part of the deviceTerminal Accommodation#12 AWG through #4 AWG copper wire onlyTerminal IdentificationTerminals identified in accordance with UL 498 and CSA

Environmental

FlammabilityUL 94 HBIP SuitabilityIP20Operating TemperaturesMaximum continuous 75°C; minimum -40°C (w/o impact)

Customer Use Drawing eCatalog

