# Twist-Lock® Devices 15A, 125V, 2 Pole, 2 Wire Non-Grounding Stainless Steel Flanged Inlet

# HUBBELL

#### **Features**

- Heat resistant thermoset construction
- Stainless steel casing
- #5-40 terminal screws
- Mounting screws included

# **Ordering Information**

Description Device Color UPC Catalog Number Stainless steel casing, Black/Stainless 783585237565 HBL7526 black phenolic.

#### Listings

Listed to UL 498

# **Specifications**

Flange Stainless steel
Contacts Brass
Terminal Screws Brass

Mounting Screw Nickel plated brass

#### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #10 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)







### **Accessories**

Plug HBL7545C

## Resources

Customer Use Drawing eCatalog

