Non-NEMA Twist-Lock® Devices 10A, 250V, 15A, 125V, 2 Pole, 3 Wire Grounding Stainless Steel Flanged Inlet



Features

- Heat resistant thermoset construction
- Stainless steel casing
- #5-40 terminal screws
- Mounting screws included

Ordering Information

Description Stainless steel casing, brown phenolic

Device Color Brown/Stainless

783585237657

Catalog Number HBL7556G

Accessories

Connector HBL7555G	

Resources

eCatalog

Specifications

Flange Stainless steel Blades **Brass**

Terminal Screws Brass

Mounting Screw Nickel plated brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

#16 AWG - #12 AWG solid or stranded copper wire only Terminal Accommodation

Terminal Identification Terminals identified in accordance with UL 498

Environmental

HB or better per UL94/CSA 22.2 No.0.17 Flammability

IP20 Suitability Moisture Resistance

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

