Midget Twist-Lock® Devices 15A, 125V AC, 2 Pole, 3 Wire Grounding Plug



Features

- Abuse resistant nylon housing
- Phenolic body for high heat resistance
- Angled body design for low profile in tight spaces
- Totally insulated body adds extra measure of safety

Ordering Information

Description Black angled plug.	Cord Diameter .335"421" (8.5-10.7)	UPC 783585237688	Catalog Number HBL7570
	()		

Listings

Listed to UL 498 Certified to CSA C22.2 No.42

Specifications

Housing	Nylon	
Blades	Brass	
Blade Holder	Phenolic	
Terminal Screws	#5-40 Brass	
Terminal Clamp	Nylon	



Electrical

Current Interrupting Dielectric Voltage Certified for current interrupting at full rated current Withstands 2,000V minimum

 Mechanical

 Terminal Accomodation
 #18 AWG - #14 AWG stranded copper wire only.

 Terminal Identification
 Terminals identified in accordance with UL 498

Environmental

FlammabilityHB or better per UL94/CSA 22.2 No.0.17Moisture ResistanceIP20 SuitabilityOperating TemperaturesMaximum Continuous 75°C Minimum -40°C (w/o impact)

Accessories

15A 125V NEMA ML-2P

Angled Connector	HBL7571
Nylon Flanged Receptacle	HBL7596N
Stainless Steel Flanged Receptacle	HBL7596
StainlessSteel Flanged Receptacle with Covered Terminals	HBL7598

STAKE

Resources

Customer Use Drawing eCatalog

