

Non-NEMA Twist-Lock® Devices
10A, 250V, 15A, 125V, 2 Pole, 3 Wire Grounding
Receptacle

HUBBELL

Features

- Thermoset construction offers high heat resistance
- High performance copper alloy contacts
- Corrosion resistant zinc plated steel one-piece mounting strap

Ordering Information

Description	Device Color	UPC	Catalog Number
Single, flush, black phenolic	Black	783585237725	HBL7582G

Listings

Listed to UL 498
Fed. Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Face	RTP
Base	Molded Thermoset
Contacts	Brass
Clamp	Brass
Ground Contact	Brass
Terminal Screws	Brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#18 AWG -#10 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Plug	HBL7567C
Wallplate or Weatherproof Cover	1.40" Boss Opening

Resources

eCatalog

