Non-NEMA Twist-Lock® Devices 10A, 250V, 15A, 125V, 3 Pole, 3 Wire Non-Grounding

Receptacle

HUBBELL

Features

- Thermoset construction offers high heat resistance
- High performance copper alloy contacts
- Corrosion resistant zinc plated steel one-piece mounting strap

Ordering Information

Description	Device Color	UPC	Catalog Number
Single, black phenolic	Black	783585237718	HBL7582

Listings

Listed to UL 498 Fed. Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Terminal Screws	Brass
Ground Contact	Brass
Clamp	Brass
Contacts	Brass
Base	Molded Thermoset
Face	RTP

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG -#10 AWG solid or stranded copper wire only.


Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Plug	HBL7567C
Wallplate or Weatherproof Cover	1.40" Boss Opening

Resources

Customer Use Drawing eCatalog

