# Midget Twist-Lock® Devices 15A, 125V AC, 2 Pole, 3 Wire Grounding Flanged Inlet

# HUBBELL

## **Features**

- Fully Insulated nylon casing with integral flange
- Black color blends in with equipment





#### **Ordering Information**

Description	Terminals	UPC	Catalog Number
Black nylon flanged	Exposed	783585237800	HBL7595N
inlet.			

## Listings

Listed to UL 498 Certified to CSA C22.2 No.42

#### **Specifications**

Flange	Nylon	
Base	Nylon	
Blades	Bronze	
Terminal Screws	#5-40 Brass	

# Performance

#### **Electrical**

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #14 AWG solid or stranded copper wire only.

Terminal Identification


Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



# **Accessories**

Valise® Connector	HBL7593V
Connector	HBL77593
Angled Connector	HBL7571

#### Resources

Customer Use Drawing eCatalog

