

Straight Blade Devices

20A 125V, 2-Pole 3-Wire, 5-20R

EdgeConnect™ HBL® Extra Heavy Duty MAX Hospital Grade Duplex Receptacle

HUBBELL

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Hospital Grade, Finder Groove Face, Back Wired	Green	78358568740	HBL8300STGN

Listings

UL Listed to UL498 File No. E2186
Certified to CSA 22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Specifications

Face	Polycarbonate
Base	Polycarbonate
Mounting Strap	Nickel Plated Brass
Ground Contact	Copper Alloy
Mounting Screws	Plated Steel

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only, Consult Factory for #10 Applications
Terminal Identification	Terminals Identified in Accordance with UL 498 and CSA

Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

